



Basic features

Scope of delivery	Fixed stop 2x nut M08x1
Short description	Fixed stop
Use	for inductive sensors $\varnothing 4$ for inductive sensors BES M8

Environmental conditions

Ambient temperature	-25...100 °C
----------------------------	--------------

Material

Material	Stainless steel
-----------------	-----------------

Mechanical data

Clamping system	Threads Clamps
Dimension	$\varnothing 8 \times 57$ mm
Life expectancy mechanical	0.5 mil. switching operations
Mounting part	Screws M8
Size	M8x1
Spring deflection	2 mm
Spring force	3 N
Stop force F max.	300 N
Tightening torque	6 Nm 12 Nm
Tightening torque max.	6 Nm 12 Nm

Remarks

Switching point between the proximity switch and trigger pin can be set wherever needed.
 Fixed stop combined with corresponding clamp cuff.