



Basic features

Scope of delivery	Fixed stop 2x nut M12x1
Short description	Fixed stop
Use	for inductive sensors Ø8 for inductive sensors BES M8

Environmental conditions

Ambient temperature	-25...100 °C
----------------------------	--------------

Material

Material	Stainless steel
-----------------	-----------------

Mechanical data

Clamping system	Threads Clamps
Dimension	Ø 12 x 78 mm
Life expectancy mechanical	0.5 mil. switching operations
Mounting part	Screws M12
Size	M12x1
Spring deflection	3 mm
Spring force	4 N
Stop force F max.	400 N
Tightening torque	25 Nm
Tightening torque max.	25 Nm

Remarks

Switching point between the proximity switch and trigger pin can be set wherever needed.
 Fixed stop combined with corresponding clamp cuff.