



## Basic features

Approval/Conformity	cULus CE WEEE
Basic standard	IEC 60947-5-2

## Display/Operation

Function indicator	yes
Power indicator	no

## Electrical connection

Cable diameter D	3.10 mm
Cable length L	0.8 m
Connection	M8x1-Male, 3-pin
Connection type	Cable with connector, 0.80 m, PUR
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

## Electrical data

Load capacitance max. at Ue	0.5 µF
Min. operating current I <sub>m</sub>	0 mA
No-load current I <sub>o</sub> max., damped	9 mA
No-load current I <sub>o</sub> max., undamped	3 mA
Operating voltage U <sub>b</sub>	10...30 VDC
Output resistance R <sub>a</sub>	33.0 kOhm + D
Protection class	II
Rated insulation voltage U <sub>i</sub>	250 V AC
Rated operating current I <sub>e</sub>	200 mA
Rated operating voltage U <sub>e</sub> DC	24 V
Rated short circuit current	100 A
Ready delay t <sub>v</sub> max.	20 ms
Residual current I <sub>r</sub> max.	20 µA
Ripple max. (% of U <sub>e</sub> )	15 %
Switching frequency	1500 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

## Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g <sub>n</sub> , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP68

## Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Inductive Sensors  
**BES 516-324-G-E4-C-S49-00,8**  
Order Code: BES03P9

# BALLUFF

## Material

Housing material	Stainless steel
Material jacket	PUR
Material sensing surface	PBT

## Mechanical data

Dimension	Ø 8 x 30 mm
Installation	for flush mounting
Size	M8x1
Tightening torque	8 Nm

## Range/Distance

Assured operating distance Sa	1.6 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	2 mm
Real switching distance sr	2 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

## Remarks

Flush: See installation instructions for inductive sensors with extended range 825357.  
The sensor is functional again after the overload has been eliminated.

## Connector Drawings



## Wiring Diagrams

