



Basic features

Application	Pneumatic cylinder with integrated groove
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Use	for magnetic sensors BMF 303

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Remarks

US Patent No. 6, 637, 279

Material

Material	Nickel silver
-----------------	---------------

Mechanical data

Mounting, holder	Threaded pin ISO 4029 M2x5-A2 Offset screwdriver ISO 2936 0.9
Sensor attachment	Threaded pin ISO 4029 M2x3-A2 offset screwdriver ISO 2936 0.9
Size	Slot 10 (Festo) C-slot (SMC-/Bimba)
Tightening torque	0.2 Nm
Tightening torque clamping screw	0.2 Nm

Help Views

