



1) Sensing surface



Basic features

Approval/Conformity	cULus CE UKCA WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Cable diameter D	3.00 mm
Cable length L	0.3 m
Conductor cross-section	0.14 mm ²
Connection	M8x1-Male, 3-pin
Connection type	Cable with connector, 0.30 m, TPE
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U _e	0.5 µF
Min. operating current I _m	0 mA
No-load current I _o max., damped	12 mA
No-load current I _o max., undamped	8 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	33.0 kOhm + D
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	10 ms
Residual current I _r max.	20 µA
Ripple max. (% of U _e)	15 %
Switching frequency	1000 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Functional safety

MTTF (40 °C)	730 a
--------------	-------

Inductive Sensors
BES Q08ZC-PSC30B-EZ00,3-GS49-519
Order Code: BES055A



Interface

Switching output PNP normally open (NO)

Material

Housing material Zinc, Die casting, coated
 Material jacket TPE, Flame-resistant
 Material sensing surface PBT, coated

Mechanical data

Dimension 40 x 8 x 8 mm
 Installation for flush mounting
 Size 8x8

Range/Distance

Assured operating distance Sa 2.4 mm
 Hysteresis H max. (% of Sr) 15.0 %
 Rated operating distance Sn 3 mm
 Real switching distance sr 3 mm
 Repeat accuracy max. (% of Sr) 5.0 %
 Switching distance marking ■■
 Temperature drift max. (% of Sr) 10 %
 Tolerance Sr ±10 %

Remarks

The sensor is functional again after the overload has been eliminated.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

