



Basic features

Application	Pneumatic cylinder with integrated groove
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening part Mounting bracket
Use	for magnetic sensors BMF 305

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Sensor attachment	Cylinder head screw DIN 7984 M3x10-A2 cylinder head screw ISO 1207 M3x10-A2
Size	T-slot
Tightening torque	1.5 Nm

Help Views

