



## Basic features

<b>Additional features</b>	Factor 1 Extended temperature range weld-immune (magnetic field 100kA/m) Housing resistant to weld spatter
<b>Approval/Conformity</b>	CE UKCA cULus WEEE
<b>Basic standard</b>	IEC 60947-5-2
<b>Scope of delivery</b>	Nut (2x)

## Display/Operation

<b>Function indicator</b>	yes
<b>Power indicator</b>	no

## Electrical connection

<b>Connection</b>	M12x1-Male, 3-pin, A-coded
<b>Polarity reversal protected</b>	yes
<b>Protection against device mix-ups</b>	yes
<b>Short-circuit protection</b>	yes

## Electrical data

<b>Load capacitance max. at Ue</b>	1 µF
<b>No-load current I<sub>o</sub> max., damped</b>	8.5 mA
<b>No-load current I<sub>o</sub> max., undamped</b>	4.5 mA
<b>Operating voltage U<sub>b</sub></b>	10...30 VDC
<b>Output resistance R<sub>a</sub></b>	33.0 kOhm + D
<b>Protection class</b>	II
<b>Rated insulation voltage U<sub>i</sub></b>	250 V AC
<b>Rated operating current I<sub>e</sub></b>	200 mA
<b>Rated operating voltage U<sub>e</sub> DC</b>	24 V
<b>Rated short circuit current</b>	100 A
<b>Ready delay t<sub>v</sub> max.</b>	3 ms
<b>Ripple max. (% of U<sub>e</sub>)</b>	15 %
<b>Switching frequency</b>	1500 Hz Measured at 2 mm, 24 V, 100 mA
<b>Utilization category</b>	DC -13
<b>Voltage drop static max.</b>	1.5 V

## Environmental conditions

<b>Ambient temperature</b>	-30...85 °C
<b>Contamination scale</b>	3
<b>EN 60068-2-27, Shock</b>	Half-sinus, 30 g <sub>n</sub> , 11 ms
<b>EN 60068-2-6, Vibration</b>	55 Hz, amplitude 1 mm, 3x30 min
<b>IP rating</b>	IP68
<b>Magnetic field immune</b>	magnetic field immune (AC/DC)

## Functional safety

<b>MTTF (40 °C)</b>	379 a
---------------------	-------

## Interface

<b>Switching output</b>	PNP normally open (NO)
-------------------------	------------------------

Inductive Sensors  
**BES M12MI-PSC30A-S04G-W09**  
**Order Code: BES05Y2**



**Material**

Housing material	Brass, PTFE coated
Material sensing surface	PBT, PTFE coated

**Mechanical data**

Dimension	Ø 12 x 65 mm
Installation	for flush mounting
Size	M12x1
Tightening torque	12 Nm

**Range/Distance**

Assured operating distance Sa	2.4 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	3 mm
Real switching distance sr	3 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

**Remarks**

The sensor is functional again after the overload has been eliminated.  
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

