



Basic features

Application	Pneumatic cylinder with integrated groove Used with BMF 303-HW-51 Holder suitable for 2 T slot dimension. For slot dimensions see drawing
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening part Mounting bracket
Use	for magnetic sensors BMF 305

Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Mounting, holder	Cylinder head screw ISO 1207 M3x14-A2
Sensor attachment	Cylinder head screw ISO 1207 M3x5-A2
Size	T-slot (SMC)
Tightening torque	1.5 Nm
Tightening torque clamping screw	0.5 Nm

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Help Views

