



## Basic features

<b>Application</b>	Pneumatic cylinder with integrated groove
<b>Basic standard</b>	Dimension tolerances: DIN ISO 2768 m
<b>Principle of operation</b>	BMF mounting bracket
<b>Scope of delivery</b>	Fastening screw Mounting bracket Offset screwdriver
<b>Style</b>	Mounting bracket
<b>Use</b>	for magnetic sensors BMF 305

## Environmental conditions

<b>Ambient temperature</b>	-40...85 °C
----------------------------	-------------

## Material

<b>Housing material</b>	Aluminium
<b>Material</b>	Aluminum

## Mechanical data

<b>Dimension</b>	Ø 12 x 6.35 mm
<b>Mounting, holder</b>	Threaded pin ISO 4029 M3x3-A2 Offset screwdriver ISO 2936 1.5
<b>Sensor attachment</b>	Cylinder head screw DIN 7984 M3x10-A2 offset screwdriver ISO 2936 2.0
<b>Size</b>	T-slot
<b>Tightening torque</b>	1.5 Nm
<b>Tightening torque clamping screw</b>	1.5 Nm