

1) Hex nut, 2) O-ring



### Basic features

<b>Application</b>	Panel connector
<b>Approval/Conformity</b>	cULus WEEE

### Electrical connection

<b>Conductor cross-section</b>	22 AWG
<b>Connection</b>	M12x1-Male, straight, 5-pin, A-coded
<b>Number of conductors</b>	5

### Electrical data

<b>Operating voltage <math>U_b</math></b>	300 VDC / 300 VAC
<b>Rated current (40 °C)</b>	4.0 A

### Environmental conditions

<b>Ambient temperature</b>	-40...105 °C
<b>IP rating</b>	IP67

### Interface

<b>Switching output</b>	Complementary
-------------------------	---------------

### Material

<b>Conductor insulation material</b>	PVC
<b>Material contacts</b>	Copper alloy
<b>Material cover nut</b>	Brass nickel-plated


### Mechanical data

<b>Lead length L</b>	0.60 m
<b>Mounting part</b>	1/4"-18 NPT
<b>Tightening torque pigtail</b>	0.6 Nm

### Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Connector Drawings



- PIN 1: brown
- PIN 2: white
- PIN 3: blue
- PIN 4: black
- PIN 5: gray

## Wiring Diagrams

