

## Basic features

Application	Welding area
Approval/Conformity	CE cULus WEEE

## Electrical connection

Bending radius min., fixed cable	7.5 x D
Bending radius min., flexible cable	15 x D
Cable	FEP welding spark resistant black, 2 m
Cable diameter D	3.75 mm $\pm$ 0.25 mm
Conductor cross-section	0.34 mm <sup>2</sup>
Connection 1	M8x1-Female, straight, 3-pin, A- coded
Connection 2	M12x1-Male, straight, 3-pin, A- coded
Number of conductors	3
System	Molded/Molded

## Electrical data

Operating voltage $U_b$	60 VDC / 60 VAC
Rated current (40 °C)	4.0 A

## Remarks

Cable construction acc. to UL-AWM Style 2749  
 Maximum temperature at outer jacket from weld spatter/beads short-time 800°C.  
 Flame-retarding  
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Environmental conditions

Cable temperature, fixed routing	-100...200 °C
Connector 01, temperature max.	100 °C
IP rating	IP65/IP65


## Material

Cable jacket material, note	welding spark resistant
Cable jacket, material	FEP
Material contact carrier	PUR, special/PUR, special
Material contacts	Bronze/Brass
Material cover nut	Brass PTFE coated/Brass PTFE coated
Material grip	PUR, special/PUR, special


## Mechanical data

Cable jacket, color	black
Cable length L	2.00 m
Tightening torque pigtail	0.4 Nm/0.6 Nm

## Connector Drawings



II  
PIN 1: brown  
PIN 3: blue  
PIN 4: black



I  
PIN 1: brown  
PIN 3: blue  
PIN 4: black

## Wiring Diagrams

