

1) Reference edge



### Basic features

<b>Approval/Conformity</b>	CE UKCA CCC WEEE
<b>Basic standard</b>	IEC 60947-5-1
<b>Operating principle</b>	1. Switch position: Mechanical
<b>Version</b>	Snap contact

### Display/Operation

<b>Function indicator</b>	1. Switch position: None
---------------------------	--------------------------

### Electrical connection

<b>Connection</b>	M12x1-Flange male, 5-pin
<b>Connection type</b>	1. Switch position: Connector

### Electrical data

<b>Continuous current</b>	1. Switch position: 0.1 A
<b>Rated operating voltage Ue</b>	1. Switch position: 250 V AC
<b>Switching function mechanical</b>	Single-pin changeover
<b>Switching rate</b>	1. Switch position: 200/min

### Environmental conditions

<b>Ambient temperature</b>	-5...85 °C
<b>IP rating</b>	IP67

### Functional safety

<b>B10d (EN ISO 13849-1)</b>	BSE 74.1: 10 mil. switching cycles
------------------------------	------------------------------------

### Material

<b>Housing material</b>	Aluminium, Anodized
<b>Housing material, surface protection</b>	Anodized
<b>Material contacts</b>	1. Switch position: Gold
<b>Plunger material</b>	1. Switch position: 1.4034 stainless steel


### Mechanical data

<b>Approach direction</b>	lateral or at right angles to mounting surface
<b>Approach speed</b>	1. Switch position: 20 m/min
<b>Dimension</b>	40 x 20 x 47 mm
<b>Distance cam - reference edge</b>	1. Switch position: 2.30...2.80 mm
<b>Flange, feed-through</b>	None
<b>Installation</b>	any
<b>Life expectancy mechanical</b>	1. Switch position: 10 mil. switching operations
<b>Number of switching positions</b>	Chisel Mechanical
<b>Plunger spacing 1st switch position</b>	10 mm
<b>Plunger style</b>	1st switch position: Chisel
<b>Switch actuation force</b>	1. Switch position: 8 N
<b>Switching element</b>	1. Switch position: BSE 74.1

### Range/Distance

<b>Reproducibility</b>	1. Switch position: ±0.02 mm
------------------------	------------------------------

## Connector Drawings



View of connector side

## Wiring Diagrams

