

1) Optical axis emitter, 2) Optical axis receiver, 3) Output function



Basic features

Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Reference reflector	BOS R-22
Series	Q08M
Style	Square Connection 90°

Display/Operation

Display	Limit range - LED yellow, flashing LED yellow: Light received
---------	--

Electrical connection

Connection	Connector, M8x1-Male, 3-pin
Contact, surface protection	Gold plated
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U_e	0.1 μ F
No-load current I_o max. at U_e	10 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	33.0 kOhm
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ready delay t_v max.	150 ms
Residual current I_r max.	50 μ A
Ripple max. (% of U_e)	10 %
Switching frequency	400 Hz
Turn-off delay t_{off} max.	1.25 ms
Turn-on delay t_{on} max.	1.25 ms
Utilization category	DC -13
Voltage drop U_d max. at I_e	1.2 V

Environmental conditions

Ambient temperature	-5...55 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 100 gn, 2 ms, 3x8000 Half-sinus, 30 gn, 11 ms, 3x6
EN 60068-2-6, Vibration	10...2000 Hz, amplitude 1 mm, 30 gn, 3x5 h 10...55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Photoelectric Sensors
BOS Q08M-PS-LR20-S49
Order Code: BOS01MP



Functional safety

MTTF (40 °C) 1619 a

Interface

Switching output PNP normally open (NO)

Material

Housing material Zinc, Die casting, nickel-plated
 Material sensing surface PMMA
 Surface protection nickel-plated

Mechanical data

Dimension 8 x 59 x 8 mm
 Mounting part Screw M3

Optical features

Ambient light max. 5000 Lux
 Average power Po max. 390 µW
 Beam characteristic Divergent
 Blind zone 25 mm
 Laser class per IEC 60825-1 1
 Light spot size Ø 3.0 mm Light exit
 Light type Laser red light
 Polarizing filter yes
 Principle of optical operation Retroreflective sensor
 Pulse duration t max. 10.0 µs
 Pulse frequency 10.8 kHz
 Pulse power Pp max. 3.1 mW
 Smallest part typ. 0.4 mm at 100 mm. R0 = 500 mm
 Switching function, optical dark-on
 Wave length 655 nm

Range/Distance

Range 0...1 m
 Rated operating distance Sn 1 m

Remarks


Order accessories separately.
 For additional information, refer to user's guide.
 Only for applications per NFPA 79 (machines with a supply voltage of maximum 600 V). Use an R/C (CYJV2) cable with suitable properties for attaching the device.
 Polarizing filters prevent spurious switching due to reflecting and shiny parts.
 The sensor is functional again after the overload has been eliminated.
 Actuation object (target): gray card, 200 x 200, 90 % remission, lateral approach, approach direction vertical to lens axis plane.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings




Wiring Diagrams



Opto Symbols



Warning Symbols



LASER CLASS 1 per IEC 60825-1