

1) Optical axis receiver, 2) Optical axis emitter, 3) Operating voltage, 4) Light reception/limit area, 5) Sn



**Basic features**

Approval/Conformity	CE UKCA cULus LISTED WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	12M
Style	Cylinder Straight optics
Trademark	Global

**Display/Operation**

Adjuster	Potentiometer 270°
Display	LED green: Power Limit range - LED yellow, flashing LED yellow: Light received
Setting	Rated switching distance (Sn)

**Electrical connection**

Cable diameter D	4.60 mm
Cable length L	2 m
Conductor cross-section	0.34 mm <sup>2</sup>
Connection	Cable, 2.00 m, PVC
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

**Electrical data**

Load capacitance max. at Ue	0.2 µF
No-load current I <sub>o</sub> max. at Ue	20 mA
Operating voltage U <sub>b</sub>	10...30 VDC
Rated insulation voltage U <sub>i</sub>	75 V DC
Rated operating current I <sub>e</sub>	100 mA
Rated operating voltage U <sub>e</sub> DC	24 V
Ripple max. (% of U <sub>e</sub> )	15 %
Switching frequency	1000 Hz
Turn-off delay t <sub>off</sub> max.	0.5 ms
Turn-on delay t <sub>on</sub> max.	0.5 ms
Utilization category	DC -13
Voltage drop U <sub>d</sub> max. at I <sub>e</sub>	1.5 V

**Environmental conditions**

Ambient temperature	-5...55 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g <sub>n</sub> , 11 ms, 3x6
EN 60068-2-6, Vibration	10...55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

**Functional safety**

MTTF (40 °C)	1427 a
--------------	--------

**Interface**

Switching output	PNP normally closed (NC)
------------------	--------------------------

Photoelectric Sensors  
**BOS 12M-PO-PR10-02**  
Order Code: **BOS01ZK**

**BALLUFF**

**Material**

Housing material	Brass, nickel-plated
Material jacket	PVC
Material sensing surface	PMMA
Surface protection	nickel-plated

**Mechanical data**

Dimension	Ø 12 x 60 mm
Mounting part	Nut M12x1
Tightening torque max.	7 Nm 15 Nm

**Optical features**

Ambient light max.	10000 Lux
Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light spot size	Ø 160 mm at 3 m
Light type	LED, red light
Polarizing filter	yes
Principle of optical operation	Retroreflective sensor
Switching function, optical	dark-on
Wave length	644 nm

**Range/Distance**


Range	0...3 m
Rated operating distance Sn	3 m Adjustable
Temperature drift max. (% of Sr)	10 %

**Remarks**

Order accessories separately.  
For additional information, refer to user's guide.  
Polarizing filters prevent spurious switching due to reflecting and shiny parts.  
The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Wiring Diagrams**



**Opto Symbols**

