


| REVISIONS | | | | |
|-----------|-----|------------------|-----------|-------|
| P | LTR | DESCRIPTION | DATE | APVD |
| | 1 | INITIAL RELEASED | 10JAN2024 | TP WH |



NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
 FREQUENCY RANGE : DC-0.5 GHz
 NOMINAL IMPEDANCE : 50 OHMS
 INSULATION RESISTANCE : 5000 MOHMS
 WORKING VOLTAGE : 500 VRMS MAX
 DIELECTRIC WITHSTANDING VOLTAGE : >1000 VOLTS MAX
- 4 MECHANICAL CHARACTERISTICS :
 DURABILITY : 500 CYCLES
- 5 TEMPERATURE RANGE: -65°-+165°;
- 6 RoHS: COMPLIANT.

| TEPN | L(mm) | IL(MAX) | VSWR |
|-----------|---------|--------------------|--------------------|
| 2479976-1 | 1600±15 | <1.15dB(DC-0.5GHz) | 1.5 MAX(DC-0.5GHz) |
| 2479976-2 | 992±8 | <0.85dB(DC-0.5GHz) | 1.5 MAX(DC-0.5GHz) |

| -7 | -6 | -5 | -4 | -3 | -2 | -1 | U/N | TEPN | DESCRIPTION | ITEM |
|----|----|----|----|----|-----|------|-----|------|--------------------|------|
| | | | | | 1 | 1 | PC | / | BNC MALE CONNECTOR | 3 |
| | | | | | 992 | 1600 | mm | / | BELDEN 9222 CABLE | 2 |
| | | | | | 1 | 1 | PC | / | BNC MALE CONNECTOR | 1 |

| | | | | | |
|--|--|--|-----|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN | TP | 10JAN2024 | |
| | | CHK | ED | 10JAN2024 | |
| | | APVD | WH | 10JAN2024 | |
| | | NAME | | | |
| DIMENSIONS: mm | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | | |
| | | 0 PLC | ± 5 | PRELIMINARY TRIAX BNC MALE S/T, BELDEN 9222 CABLE,50ohm | |
| | | 1 PLC | ± - | SEE NOTES | |
| | | 2 PLC | ± - | APPLICATION SPEC | |
| | | 3 PLC | ± - | PRODUCT SPEC | |
| | | 4 PLC | ± - | SIZE CAGE CODE DRAWING NO RESTRICTED TO | |
| | | ANGLES | ± 5 | - A3 00779 C-2480557 - | |
| MATERIAL SEE TABLE | | FINISH - | | WEIGHT 0 | |
| | | | | CUSTOMER DRAWING SCALE 1:1 SHEET 1 OF 1 REV 1 | |