


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL RELEASED	10JAN2024	TP	WH



NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
 FREQUENCY RANGE : DC-6 GHz
 NOMINAL IMPEDANCE : 50 OHMS
 INSULATION RESISTANCE : >1000 MOHMS
 WORKING VOLTAGE : 335 VRMS MAX
 DIELECTRIC WITHSTANDING VOLTAGE : >1000 VOLTS MAX
- 4 MECHANICAL CHARACTERISTICS :
 DURABILITY : 500 CYCLES
- 5 TEMPERATURE RANGE: -45°-+125°
- 6 RoHS: COMPLIANT.

TEPN	L(mm)	IL(MAX)	VSWR
2480655-1	153±6	<0.9dB(DC-6GHz)	1.35 MAX(DC-6GHz)
2480655-2	305±10	<1.30dB(DC-6GHz)	1.35 MAX(DC-6GHz)

-7	-6	-5	-4	-3	-2	-1	U/N	TEPN	DESCRIPTION	ITEM
					2	2	PC	/	HEAT SHRINK(BLACK)	4
					1	1	PC	/	MCX MALE CONNECTOR	3
					305	153	mm	/	RG316 CABLE	2
					1	1	PC	/	MCX MALE CONNECTOR	1
QUANTITY PER ASSY										PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 5 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 5	DWN TP 10JAN2024 CHK ED 10JAN2024 APVD WH 10JAN2024	NAME
MATERIAL SEE TABLE	FINISH -	PRODUCT SPEC SEE NOTES	APPLYING SPEC
		SIZE A3	CAGE CODE 00779
		DRAWING NO C-2480655	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1
		REV 1	

PRELIMINARY

STE

TE Connectivity

MCX MALE R/T TO MCX MALE R/T
RG316 CABLE,50 ohm