



Basic features

Application	Pneumatic cylinder with integrated groove Mannesmann-Rexroth green Series
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Use	for magnetic sensors BMF 305

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Mounting, holder	Threaded pin ISO 4027 M3x4-A2 Offset screwdriver ISO 2936 1.5
Sensor attachment	Cylinder head screw DIN 7984 M3x5-A2 offset screwdriver ISO 2936 2.0
Size	L-slot
Tightening torque	1.5 Nm
Tightening torque clamping screw	1.5 Nm

Help Views

