



Basic features

Use	for photoelectric retroreflective sensors
Version	Cube corner 4 mm

Environmental conditions

Ambient temperature	-20...100 °C
----------------------------	--------------

Material

Housing material	PC
Material sensing surface	PC

Remarks

The degree of reflection is at maximum for vertical light infall and when the reflector is at an optimum orientation to the light polarization direction.

Mechanical data

Dimension	Ø 51 x 7.4 mm
Mounting part	Diameter 6.0 mm
Sensing surface	17.7 cm ²

Optical features

Light type	non-polarized light, also for polarized light
-------------------	---