


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
1		INITIAL RELEASED	11JAN2024	TP WH



NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
 FREQUENCY RANGE : DC-6 GHz
 NOMINAL IMPEDANCE : 50 OHMS
 INSULATION RESISTANCE : >1000 MOHMS
 WORKING VOLTAGE : 175 VRMS MAX
 DIELECTRIC WITHSTANDING VOLTAGE : >500 VOLTS
- 4 MECHANICAL CHARACTERISTICS :
 DURABILITY : 500 CYCLES
- 5 TEMPERATURE RANGE: -55°-+155°
- 6 RoHS: COMPLIANT.

TEPN	L(mm)	IL(MAX)	VSWR
2480671-1	152.4±3	<1.65dB(DC-6GHz)	1.30 MAX(DC-6GHz)

QTY	UNIT	DESCRIPTION	ITEM							
2	PC	HEAT SHRINK	4							
1	PC	MMCX MALE CONNECTOR	3							
152.4	mm	RG178 CABLE	2							
1	PC	MMCX MALE CONNECTOR	1							
-7	-6	-5	-4	-3	-2	-1	U/N	TEPN	DESCRIPTION	ITEM
QUANTITY PER ASSY								PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TP	11JAN2024	 TE Connectivity <h1 style="margin: 0;">PRELIMINARY</h1>											
DIMENSIONS: mm		CHK ED	11JAN2024												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD WH	11JAN2024												
<table border="0"> <tr><td>0 PLC</td><td>± 5</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± 5</td></tr> </table>		0 PLC	± 5		1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± 5	NAME
0 PLC	± 5														
1 PLC	± -														
2 PLC	± -														
3 PLC	± -														
4 PLC	± -														
ANGLES	± 5														
MATERIAL SEE TBL		FINISH -		PRODUCT SPEC -											
SEE TBL		-		APPLICATION SPEC -											
-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO										
-		0	A300779	C-2480671	-										
CUSTOMER DRAWING			SCALE	SHEET	REV										
-			1:1	1 OF 1	1										