



Basic features

Component	Linear cam
Principle of operation	Cams (mechanical)

Material

Material sensing surface	Steel
Surface	Bronzed
Surface hardened	HRC 63±2

Mechanical data

Clamping system	Expansion clamp
Fine-adjustable	no
Foot shape for	U-slot
Foot width	4.00 mm
Height above cam tray	10.00 mm
Switching surface, length (L)	40 mm
Use for cam tray	BNL 5308-100-... BNL 5306-100-... BNL 5304-080-...
Use for switch position spacing	10 mm 8 mm
Width of switching area	7.50 mm
Working principle	Mechanical