



Basic features

Principle of operation	Clamp holder
Scope of delivery	Fixed stop Screw ISO 4762-M5x18 (2x)
Use	for sensors Ø12 mm For M12 sensors
Version	Mounting clamp

Environmental conditions

Ambient temperature	-25...100 °C
----------------------------	--------------

Remarks

The fixed stop may alter the switching distance of the proximity switch.

Material

Material	Stainless steel
-----------------	-----------------

Mechanical data

Clamping system	Threads
Dimension	38 x 19 x 35 mm
Mounting part	Screws, clamps
Tightening torque max.	1.5 Nm