

### Basic features

Application	Profinet , CAT 5
Approval/Conformity	CE UKCA cULus WEEE

### Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	15 x D
Cable	PUR Shielded Green, 35 m, drag chain compatible
Cable diameter D	6.70 mm ±0.30 mm
Cable, bending cycles min.	2 mil.
Cable, note	Profinet Type C, CAT 5E by IEC 61156-6
Conductor cross-section	22 AWG
Connection 1	M12x1-Male, straight, 4-pin, D-coded
Connection 2	RJ45-Male, straight, 4-pin
Number of conductors	4
System	Molded/assembled

### Electrical data

Operating voltage $U_b$	60 VDC
Rated current (40 °C)	1.5 A
Transfer rate	10/100 Mbit/s

### Environmental conditions

Cable temperature, fixed routing	-40...80 °C
Cable temperature, flexible routing	-20...60 °C
IP rating	IP67/IP20

### Material

Cable jacket material, note	Shielded
Cable jacket, material	PUR
Cable shield	Aluminum foil and copper braid
Material contact carrier	PUR
Material contacts	Brass
Material cover nut	Brass
	nickel-plated
Material grip	PUR/PA



### Mechanical data

Acceleration max., drag chain	2 m/s <sup>2</sup>
Cable jacket, color	Green
Cable length L	35.00 m
Cable properties	drag chain compatible
Horizontal travel permitted, drag chain	5 m
Tightening torque pigtail	0.6 Nm/-
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	5 m

Remarks


Cable construction acc. to UL-AWM Style 20549  
 Halogen-free per DIN VDE 0472 Part 815  
 Silicone-free  
 Flame resistance acc. to FT1  
 Enclosure rating per IEC 60529 or ISO 20653, only in screwed state with the associated mating piece.

Connector Drawings



- |                 |               |
|-----------------|---------------|
| II              | I             |
| PIN 1: yellow   | PIN 1: yellow |
| PIN 2: orange   | PIN 2: white  |
| PIN 3: white    | PIN 3: orange |
| PIN 4: not used | PIN 4: blue   |
| PIN 5: not used |               |
| PIN 6: blue     |               |
| PIN 7: not used |               |
| PIN 8: not used |               |

Wiring Diagrams (Schematic)



- 1) Shield on cover nut  
 2) Shield on housing