



### Basic features

|                               |                                                                           |
|-------------------------------|---------------------------------------------------------------------------|
| <b>Principle of operation</b> | Clamp holder                                                              |
| <b>Scope of delivery</b>      | Clamp holder (1x)<br>Nut DIN 1763-M16x1 (2x)                              |
| <b>Use</b>                    | for sensors Ø12 mm<br>For M12 sensors<br>fastening length 46mm and longer |

### Material

|                           |               |
|---------------------------|---------------|
| <b>Material</b>           | Brass         |
| <b>Surface protection</b> | nickel-plated |

### Mechanical data

|                                         |                |
|-----------------------------------------|----------------|
| <b>Dimension</b>                        | Ø 22 x 44.5 mm |
| <b>Mounting part</b>                    | Screws, clamps |
| <b>Tightening torque</b>                | 20 Nm          |
| <b>Tightening torque clamping screw</b> | 1.5 Nm         |

### Remarks

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using the compression screw.  
 The fixed stop may alter the switching distance of the proximity switch.