



Basic features

Principle of operation	Clamp holder
Scope of delivery	Clamp holder (1x) Nut DIN 1763-M12x1 (2x)
Use	for sensors Ø8 mm For M08 sensors fastening length 50mm and longer

Material

Material	Brass
Surface protection	nickel-plated

Mechanical data

Dimension	Ø 17 x 48.5 mm
Mounting part	Screws, clamps
Tightening torque	15 Nm
Tightening torque clamping screw	1 Nm

Remarks

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using the compression screw.
 The fixed stop may alter the switching distance of the proximity switch.