



Basic features

Additional features	THA
Approval/Conformity	cULus CE UKCA WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Inductive sensor

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	1 µF
Min. operating current Im	0 mA
No-load current Io max., damped	30 mA
No-load current Io max., undamped	30 mA
Operating voltage Ub	10...30 VDC
Output resistance Ra	2.7 kOhm + D + LED/4.7 kOhm + D
Rated insulation voltage Ui	75 V DC
Rated operating current Ie	130 mA
Rated operating voltage Ue DC	24 V
Rated short circuit current	100 A
Ready delay tv max.	10 ms
Residual current Ir max.	80 µA
Ripple max. (% of Ue)	15 %
Switching frequency	500 Hz
Utilization category	DC -13
Voltage drop static max.	3.5 V

Inductive Sensors
BES 517-142-Y-RK
Order Code: BES02MN



Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67, only installed in multiple limit switches

Functional safety

MTTF (40 °C)	1255 a
--------------	--------

Interface

Switching output	PNP normally open/normally closed (NO/NC)
------------------	---

Material

Housing material	PA 12
Material sensing surface	PBT

Mechanical data

Connection cross-section	2.5 mm ²
Dimension	60 x 15.5 x 57.9 mm
Installation	for flush mounting
Tightening torque	0.5 Nm

Range/Distance

Assured operating distance Sa	4 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	5 mm
Real switching distance sr	5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

Insert element must be installed in aluminum housing.
The sensor is functional again after the overload has been eliminated.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams (Schematic)

