


9136511D0RV



1) Emitter, 2) Receiver, 3) Optical axis



Basic features

Approval/Conformity	CE UKCA WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Optical sensor head
Reference base unit	BAE SA-OH-059-...
Series	M03
Style	Cylinder Straight optics

Electrical connection

Cable diameter D	1.80 mm
Cable length L	1 m
Connection	Cable with connector, M8x1- Female, 1 m, PUR
Contact, surface protection	Gold plated

Environmental conditions

Ambient temperature	-10...55 °C
IP rating	IP65

Interface

Switching output	for switching amplifier
------------------	-------------------------

Remarks

Reference object (target): gray card, 100 x 100, 90 % remission, axial approach.
For additional information, refer to user's guide.

Material

Housing material	Stainless steel
Material jacket	PUR
Material sensing surface	Epoxy

Mechanical data

Dimension	$\varnothing 3 \times 8$ mm
Mounting part	M3 nut


Optical features

Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light spot size	$\varnothing 30$ mm at 100 mm
Light type	LED infrared
Principle of optical operation	Through-beam sensor
Smallest part typ.	0.2 mm
Wave length	870 nm

Range/Distance

Range	0...800 mm
Rated operating distance Sn	800 mm

Connector Drawings



Opto Symbols

