



Basic features

Principle of operation Cams (inductive)

Material

Housing material Steel, Bronzed
 PA 6.6, Fiberglass
 Material sensing surface Steel
 Surface protection Bronzed

Mechanical data

Clamping system Expansion clamp
 Foot shape for U-slot
 Foot width 6.00 mm
 Height above cam tray 12.00 mm
 Switching surface, length (L) 50 mm

Mechanical Accessories
BEN 516-14-50
Order Code: BEN001E

BALLUFF

Use for cam tray

BNL 5307-160-...
BNL 5307-120-...
BNL 5304-160-...
BNL 5304-120-...

Use for switch position spacing

12 mm

16 mm

Width of switching area

10.00 mm