



**Basic features**

Component	Linear cam
Per DIN 69639	yes
Principle of operation	Cams (mechanical)

**Material**

Material sensing surface	Steel
Surface	Bronzed
Surface hardened	HRC 63±2

**Mechanical data**

Clamping system	Compression clamp
Fine-adjustable	no
Foot shape for	U-slot
Foot width	5.90 mm
Height above cam tray	12.60 mm
Switching surface, length (L)	100 mm
Use for cam tray	BNL 5307-160-... BNL 5307-120-... BNL 5304-160-... BNL 5304-120-...
Use for switch position spacing	16 mm 12 mm
Width of switching area	11.00 mm
Working principle	Mechanical