

**Basic features**

Approval/Conformity	CE UKCA cULus WEEE
---------------------	-----------------------------

**Display/Operation**

Power indicator	no/no
-----------------	-------

**Electrical connection**

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	15 x D
Cable	PUR Shielded Green, 5 m
Cable diameter D	6.70 mm ±0.20 mm
Cable, bending cycles min.	2 mil.
Conductor cross-section	0.34 mm <sup>2</sup>
Connection 1	M12x1-Female, straight, 4-pin, D-coded
Connection 2	RJ45-Male, straight, 4-pin
Connector 01, version	straight
Connector 02, version	straight
Number of conductors	4
Number of pins	4/4
System	Molded/Molded

**Electrical data**

Operating voltage Ub	60 VDC / 50 VAC
----------------------	-----------------

**Environmental conditions**

Cable temperature, drag chain	-20...60 °C
Cable temperature, flexible routing	-20...60 °C
IP rating	IP67/IP20

**Material**

Cable jacket material, note	Shielded
Cable jacket, material	PUR
Material contact carrier	PUR/PUR
Material contacts	Brass/Brass
Material grip	PUR/PUR


**Mechanical data**

Acceleration max., drag chain	2 m/s <sup>2</sup>
Cable jacket, color	Green
Cable length L	5.00 m
Horizontal travel permitted, drag chain	5 m at 5 m/s <sup>2</sup>
Mounting part	PG9
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	5 m at 5 m/s <sup>2</sup>


**Remarks**

Halogen-free

## Connector Drawings




- I  
 PIN 1: yellow  
 PIN 2: white  
 PIN 3: orange  
 PIN 4: blue



- II  
 PIN 1: yellow  
 PIN 2: orange  
 PIN 3: white  
 PIN 4: not used  
 PIN 5: not used  
 PIN 6: blue  
 PIN 7: not used  
 PIN 8: not used

## Wiring Diagrams (Schematic)



- 1) Shield on cover nut  
 2) Shield on housing