

1) SP1 active / error, 2) SP1: recvr., light/dark, 3) SP2 active / error, 4) SP2: recvr., light/dark, 5) Pneumatics connection PK-3



Basic features

Additional features	Contamination compensation to up to 10% loss in intensity.
Approval/Conformity	CE UKCA WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Fork sensor
Series	C
Style	Fork Straight connection

Display/Operation

Adjuster	Key (2x)
Display	Error - 2 x LED yellow, flashing Switchpoint 1 - LED yellow Switchpoint 2 - LED yellow
Setting	Light-on/dark-on Sensitivity, 2 values

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Polarity reversal protected	yes

Electrical data

Load capacitance max. at Ue	2.2 µF
No-load current I_o max. at Ue	30 mA
Operating voltage U_b	18...30 VDC
Rated operating voltage U_e DC	24 V
Ripple max. (% of U_e)	10 %
Utilization category	DC -13
Voltage drop U_d max. at I_e	1 V

Environmental conditions

Ambient temperature	-5...55 °C
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms, 3x6
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP65

IO-Link

IO-Link Profil IDs	N/A
--------------------	-----

Interface

Interface	IO-Link
-----------	---------

Material

Housing material	Aluminium, Anodized
Material sensing surface	PMMA
Surface protection	Anodized

Mechanical data

Dimension	18 x 100 x 93.5 mm
Fork opening	50 mm
Mounting part	Screw M5

Optical features

Ambient light max.	5000 Lux
Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light beams, number	10
Light spot size	3 x 28 mm Light exit
Light type	LED, red light
Principle of optical operation	Through-beam sensor
Special optical feature	Light array
Switching function, optical	dark-on/light-on
Wave length	633 nm

Range/Distance

Active length AL 1	28 mm
Hysteresis H max.	0.4 mm
Repeat accuracy lateral max.	150 µm
Resolution	≤ 0.08 mm


Remarks

Do not press key using a pointed tool.
 Order accessories separately.
 For additional information, refer to user's guide.
 Reference object (target): Steel plate, 50 x 50, thickness 0.5 mm, lateral approach.

Connector Drawings



Wiring Diagrams (Schematic)



Opto Symbols

