

4

3

2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2009
 © COPYRIGHT 2009 ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B	BB	INITIAL RELEASE	18NOV2015	KR TN

NOTES:

1. RATED POWER: 750W
2. TEMPERATURE COEFFICIENT OF RESISTANCE: $< \pm 400 \text{ppm}/^\circ\text{C}$
3. INSULATION RESISTANCE DC 500V - 20 M Ohms MIN.
4. FAULT CONDITION: 11kW FOR 3 SECONDS
5. FOR FURTHER INFORMATION SEE DATASHEET FOR TE SERIES HIGH POWER WIRE WOUND RESISTOR
6. FOR SPECIFIC PART NUMBER, RESISTANCE VALUE AND TOLERANCE PLEASE REFER TO SMART PART SEARCH

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 16NOV2015	 TE Connectivity	
DIMENSIONS: mm		CHK ALLAN P 16NOV2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TONY N 16NOV2015	TE 750 SERIES	
0 PLC ±0.5		PRODUCT SPEC	SIZE	CAGE CODE
1 PLC ±0.1		APPLICATION SPEC	A2	00779
2 PLC ±0.05		WEIGHT	DRAWING NO C-1879452	
3 PLC ±		RESTRICTED TO	-	
4 PLC ±		SCALE	1:1	
ANGLES ±0.5°		SHEET	1 OF 1	
FINISH		REV	BB	
MATERIAL		Customer Drawing		

1471-9 (3/11)