



### Basic features

<b>Principle of operation</b>	Clamp holder
<b>Scope of delivery</b>	Clamp holder (1x) Nut DIN 1763-M12x1 (2x)
<b>Use</b>	For M08 sensors for sensors Ø8 mm fastening length 28mm and longer

### Material

<b>Material</b>	Brass
<b>Surface protection</b>	nickel-plated

### Mechanical data

<b>Dimension</b>	Ø 19.5 x 28 mm
<b>Mounting part</b>	Screws, clamps
<b>Tightening torque</b>	17 Nm
<b>Tightening torque knurled nut</b>	2 Nm

### Remarks

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using the knurled nut.  
 The fixed stop may alter the switching distance of the proximity switch.