






SPECIFICATIONS:

- 1.Material:
- A Single Body:PA66 UL94 V-0
 - B Middle Cover: PA66 UL94 V-0
 - C Single Terminal: Brass Tin plated
 - D Cover: PA66 UL94 V-0
 - E Spring: Stainless Steel
 - F Button: PA66 UL94 V-0
- 2.Wire Size: 26 to 14AWG
- 3.Rating: 300V ,10A
- 4.Wire strip length:11.00mm
- 5.Power Frequency withstand:AC 2500V for 1 minute
- 6.Insulation resistance: DC 500V,500MΩ
- 7.Rated Impulse Voltage:4000V ±5 times each.
- 8.Operating Temperature:-40 to +105°
- 9.Pitch: 7.50mm (.295 in.)
10. Dims shown are for reference only

ENGINEERING LEGEND
M240-00-4-XX-M4
SERIES STYLE | POLES COLOR
PITCH

PART NUMBER DATA							
CIRCUITS	PART NUMBER	ENGINEERING NUMBER	COLOR	A IN mm		B IN mm	
2	397000502	M240-00-4-02-M4	LIGHT GRAY	.57	14.5	.295	7.50
3	397000503	M240-00-4-03-M4		.87	22.0	.591	15.00
4	397000504	M240-00-4-04-M4		1.16	29.5	.886	22.50
5	397000505	M240-00-4-05-M4		1.46	37.0	1.181	30.00
6	397000506	M240-00-4-06-M4		1.75	44.5	1.476	37.50

RELEASED EC NO.: IPG2014-0570 DRWN: RSTONE 2013/10/18 CHKD: G FARNSW APPR: JFMURPHY 2013/12/26 A	DESCRIPTION	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY RSTONE	DATE 2013/10/18	TITLE SPRING TERMINAL BLOCK 7.5MM, 45 DEG-MODULAR ----					
			4 PLACES	±---	±---	CHECKED BY G FARNSW	DATE 2013/12/20						
			3 PLACES	±---	±.005	APPROVED BY JFMURPHY		DATE 2013/12/26	molex MOLEX INCORPORATED				
			2 PLACES	±0.13	±.01								
			1 PLACE	±0.3	±---	DOCUMENT NO. SD-39700-005							
			ANGULAR ±---°										
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		SHEET NO. 1 OF 1					
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						