






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	05MAR2015	DW	CW



4X M3 THREAD, RECOMMENDED TIGHTENING TORQUE 0.5Nm



PANEL CUT FOR INSERTS FOR USE WITHOUT HOODS/ HOUSINGS




NOTES:

- TECHNICAL CHARACTERISTICS:  
 INSULATION MATERIAL: PC  
 RATED VOLTAGE: 400 V  
 RATED CURRENT: 16 A  
 INSULATION RESISTANCE:  $\geq 400M\Omega$   
 RATED IMPULSE VOLTAGE: 6 KV  
 POLLUTION DEGREE: 3  
 CONTACT RESISTANCE:  $\leq 5 m\Omega$   
 FLAMMABILITY: UL94V-0  
 MATING CYCLES: 200 FOR SILVER PLATED  
 500 FOR GOLD PLATED  
 OPERATION TEMPERATURE:  $-40-+125^{\circ}C$   
 WIRE RANGE: 0.14-4 mm<sup>2</sup> (26-12 AWG)  
 CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.

注释:

- 技术参数:  
 绝缘材料: PC  
 额定电压: 400V  
 额定电流: 16A  
 绝缘电阻:  $\geq 400M\Omega$   
 额定脉冲电压: 6 KV  
 污染等级: 3  
 接触电阻:  $\leq 5 m\Omega$   
 阻燃等级: UL94V-0  
 插拔次数: 镀银端子: 200次  
 镀金端子: 500次  
 工作温度:  $-40-+125^{\circ}C$   
 接线范围: 0.14-4 mm<sup>2</sup> (26-12 AWG)  
 接线类型: 冷压接
- 端子需要单独订购.

HEEE-072-M	T2050722101-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05MAR2015 David Wang		 TE Connectivity NAME HEEE-072-M	
DIMENSIONS: mm		CHK 05MAR2015 Chris Wang			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 05MAR2015 Xiang Xu			
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-137068			
MATERIAL		FINISH		APPLICATION SPEC 108-137068	
-		-		WEIGHT -	
-		-		Customer Drawing	

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	T2050722101000	-

SCALE 1:1 SHEET 1 OF 1 REV A