



1) Sensing surface



### Basic features

|                                |                                      |
|--------------------------------|--------------------------------------|
| Application                    | miniaturized actuators               |
| Approval/Conformity            | cULus<br>CE<br>UKCA<br>WEEE          |
| Basic standard                 | IEC 60947-5-2                        |
| Not incl. in scope of delivery | Mounting bracket, e.g. BMF 303-HW-28 |
| Principle of operation         | Magnetic field sensor                |

### Display/Operation

|                    |     |
|--------------------|-----|
| Function indicator | yes |
|--------------------|-----|

### Electrical connection

|                                   |                      |
|-----------------------------------|----------------------|
| Cable diameter D                  | 2.50 mm              |
| Cable jacket, material            | PUR                  |
| Cable length L                    | 2.00 m               |
| Conductor cross-section           | 0.10 mm <sup>2</sup> |
| Number of conductors              | 3                    |
| Polarity reversal protected       | yes                  |
| Protection against device mix-ups | yes                  |
| Short-circuit protection          | yes                  |

### Electrical data

|   |             |
|---|-------------|
| Assured switching field strength Ha           | 2 kA/m      |
| Hysteresis H max. (% of Hn)                   | 45 %        |
| Load capacitance max. at Ue                   | 1 µF        |
| No-load current I <sub>o</sub> max., undamped | 3.5 mA      |
| Operating voltage U <sub>b</sub>              | 10...30 VDC |
| Output resistance R <sub>a</sub>              | Open drain  |
| Rated insulation voltage U <sub>i</sub>       | 75 V DC     |
| Rated operating current I <sub>e</sub>        | 100 mA      |
| Rated operating voltage U <sub>e</sub> DC     | 24 V        |
| Rated short circuit current                   | 100 A       |
| Rated switch field strength H <sub>n</sub>    | 1.2 kA/m    |
| Residual current I <sub>r</sub> max.          | 10 µA       |
| Ripple max. (% of U <sub>e</sub> )            | 15 %        |
| Switching frequency                           | 30000 Hz    |
| Turn-off delay t <sub>off</sub> max.          | 0.02 ms     |
| Turn-on delay t <sub>on</sub> max.            | 0.02 ms     |
| Utilization category                          | DC -13      |
| Voltage drop static max.                      | 1 V         |

### Environmental conditions

|                         |                                       |
|-------------------------|---------------------------------------|
| Ambient temperature     | -25...85 °C                           |
| Contamination scale     | 3                                     |
| EN 60068-2-27, Shock    | Half-sinus, 30 g <sub>n</sub> , 11 ms |
| EN 60068-2-6, Vibration | 55 Hz, amplitude 1 mm, 3x30 min       |
| ESD                     | 2A (4 kV)                             |
| Emission                | Group 1, Class B                      |
| IP rating               | IP67                                  |

## Functional safety

MTTF (40 °C) 744 a

## Interface

Switching output PNP normally open (NO)

## Material

Housing material LCP  
Material jacket PUR  
Material sensing surface LCP

## Mechanical data

Dimension 25.5 x 3 x 4.5 mm  
Mounting part Mounting bracket BMF 303-HW\*

## Remarks

Max. pull force on cable 10 N.  
The sensor is functional again after the overload has been eliminated.  
Switching frequency f max.: Measured at 50 % duty cycle and 20 % I<sub>e</sub>  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Wiring Diagrams (Schematic)

