







D

C

B


A



1.98	.078	9.14	.360	—	—
1.85	.073	7.37	.290	57.02	2.245
1.57	.062	6.35	.250	46.48	1.830
1.52	.060	4.57	.180	39.37	1.550
0.38	.015	4.06	.160	31.75	1.250
0.25	.010	3.81	.150	25.40	1.000
0.13	.005	2.54	.100	19.05	.750
0.08	.003	2.29	.090	17.27	.680
.00127	.000050	2.24	.088	12.83	.505
.00076	.000030	2.11	.083	12.70	.500
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

- PARTS COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-5.
- CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES,BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- OPTIONAL CONSTRUCTION MAY DELETE THIS RIB.
- FLAMMABILITY UL V-0 FOR THICKNESS 0.4, 0.45, 0.8, 1.6, AND 3.0 PER IEC 60695-11-10.
- GLOW WIRE FLAMMABILITY (GWFI): 960°C FOR THICKNESS 0.45, 0.8, 1.6, AND 3.0 PER IEC 60695-2-12.
- GLOW WIRE IGNITION (GWIT): 825°C FOR THICKNESS 0.45, 800°C FOR THICKNESS 0.8, 775°C FOR THICKNESS 1.6 AND 3.0 PER IEC 60695-2-13.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25JAN2016	PH BRZ TIN NYLON, UL V-0 GW		1969812-1
		CHK	25JAN2016	CONTACT		HOUSING
		APVD	25JAN2016	NAME		PART NO
		PRODUCT SPEC		TE Connectivity		
		APPLICATION SPEC		PIN HEADER ASSEMBLY, RIGHT ANGLE MOUNT,6 POSITION, UNIVERSAL MATE-N-LOK(TM)		
		WEIGHT	—	SIZE		CAVE CODE
				DRAWING NO		RESTRICTED TO
				A100779		1969812
				CUSTOMER DRAWING		SCALE
				4:1		SHEET
				1 OF 1		REV
				A		