

# CONFIDENTIAL



## PRELIMINARY

NOT RELEASED FOR PRODUCTION

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS, HARRISBURG, PA.

### REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
1		INITIAL CONCEPT	07APR2016	VL	
2		ADD NOTE 2, UPDATE TABLE	28JUL2016	VL	
3		REMOVE CORNER HOLE	01SEP2016	VL	SS



SCALE 2:1

### NOTES:

- 1 MATERIAL: 0.20mm CRS. 1,25 - 3.00µm MATTE TIN FINISH.
- 2 MATERIAL: 0.20mm AL. 1.20 - 2.00µm MATTE TIN FINISH OVER NICKEL FLASH.
- 3 STAMPING BURR OUTSIDE OF PART, MAX 0.05mm.
- 4 PARTS TO BE FREE OF OIL AND CONTAMINENTS.
- 5 PART IS RoHS COMPLIANT PER TE CONNECTIVITY STANDARD TEC-138-702.
- 6 REFER TO 3D MODEL FOR UNSPECIFIED DIMENSIONS.
- 7 PACKAGING: TAPE AND REEL

7	2	2118709-4
7	1	2118709-2
PACKAGING	MATERIAL	PART NUMBER

0.10 ALL SURFACES

4X 2.50

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 07APR2016

PRELIMINARY STE TE Connectivity 1 PIECE STANDARD SHIELD

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0.20
	1 PLC ±0.15
	2 PLC ±0.10
	3 PLC ±
	4 PLC ±
	ANGLES ±2
MATERIAL SEE TABLE	FINISH SEE TABLE

PRODUCT SPEC	NAME	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-	A3	-	C-2118709	-
APPLICATION SPEC	WEIGHT	CUSTOMER DRAWING	SCALE	SHEET	REV
-	-	-	3:1	1 OF 3	3

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

# CONFIDENTIAL



## PRELIMINARY

NOT RELEASED FOR PRODUCTION

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS, HARRISBURG, PA.



NOTES:  
8. STENCIL THICKNESS: 0.10mm MIN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	07APR2016		 TE Connectivity
DIMENSIONS: mm		CHK			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 1 PIECE STANDARD SHIELD	
		0 PLC	±0.20	PRODUCT SPEC	
MATERIAL		1 PLC	±0.15	APPLICATION SPEC	
		2 PLC	±0.10	-	
		3 PLC	±	SIZE	
		4 PLC	±	CAGE CODE	
		ANGLES	±2	DRAWING NO	
		FINISH	-	G-2118709	
			-	RESTRICTED TO	
			-	-	
			-	CUSTOMER DRAWING	
			-	SCALE 1:1 SHEET 2 OF 3 REV 3	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

# CONFIDENTIAL

## PRELIMINARY



NOT RELEASED FOR PRODUCTION

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS, HARRISBURG, PA.

### PACKAGING DETAILS TBD

NOTES:

- 9. REEL SIZE: TBD
- 10. QTY PER REEL: TBD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	07APR2016		 TE Connectivity			
DIMENSIONS: mm		CHK	-					
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		0 PLC ±0.20 1 PLC ±0.15 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±2		1 PIECE STANDARD SHIELD				
MATERIAL	FINISH	PRODUCT SPEC	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-	APPLICATION SPEC	-		A3	-	C-2118709	-
-	-	WEIGHT	-		CUSTOMER DRAWING		SCALE	SHEET
				3:1	3	OF 3	REV 3	