



1) Sensing surface



### Basic features

Application	Optimized response path especially suited for short-stroke cylinders.
Approval/Conformity	cULus CE UKCA WEEE
Basic standard	IEC 60947-5-2
Not incl. in scope of delivery	Mounting bracket, e.g. BMF 103-HW-42
Principle of operation	Magnetic field sensor

### Display/Operation

Function indicator	yes
--------------------	-----

### Electrical connection

Cable diameter D	2.50 mm
Cable jacket, material	PUR
Cable length L	0.20 m
Connection	M8x1-Male, 3-pin
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Assured switching field strength $H_a$	2 kA/m
Hysteresis $H$ max. (% of $H_n$ )	45 %
Load capacitance max. at $U_e$	1 $\mu$ F
No-load current $I_o$ max., undamped	3.5 mA
Operating voltage $U_b$	10...30 VDC
Output resistance $R_a$	Open drain
Rated insulation voltage $U_i$	75 V DC
Rated operating current $I_e$	100 mA
Rated operating voltage $U_e$ DC	24 V
Rated short circuit current	100 A
Rated switch field strength $H_n$	1.2 kA/m
Residual current $I_r$ max.	10 $\mu$ A
Ripple max. (% of $U_e$ )	15 %
Switching frequency	30000 Hz
Turn-off delay $t_{off}$ max.	0.02 ms
Turn-on delay $t_{on}$ max.	0.02 ms
Utilization category	DC -13
Voltage drop static max.	1 V

### Environmental conditions

Ambient temperature	-25...85 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 $g_n$ , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
ESD	2A (4 kV)
Emission	Group 1, Class B
IP rating	IP67

## Functional safety

MTTF (40 °C) 739 a

## Interface

Switching output PNP normally open (NO)

## Material

Housing material PBT  
Material jacket PUR  
Material sensing surface PBT

## Mechanical data

Dimension 9 x 4.8 x 16 mm

## Remarks

Switching frequency f max.: Measured at 50 % duty cycle and 20 % I<sub>e</sub>  
The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Connector Drawings



## Wiring Diagrams (Schematic)

