





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		H4	ECR-14-014331	25SEP14	PKS	RRP

IDENTIFICATION NUMBER FOR MAGNET WIRE RANGE



- 1 FOR MAG-MATE CAVITY SPECIFICATION REFER TO APPLICATION SPEC #114-2066.
- 2 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON .330 CENTERS.
- 3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR MAG-MATE MUST BE POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- 4 FOR COPPER OR ALUMINUM WIRE. 2 WIRES MAX OF THE SAME SIZE AND TYPE PER SLOT
- 5 VARNISH RESIST OVER TIN PER ASTM-B545.
- 6 COPPER MAGNET WIRE ONLY. 2 WIRES MAX OF THE SAME SIZE AND TYPE PER SLOT.
- 7 PRELIMINARY - NOT FOR PRODUCTION.



OBsolete	FINISH	PART NO
6 N/A	#15-#16 UNPLATED	7 63459-5
#14-#15	#15-#16 SPECIAL	5 63459-4
#14-#15	#15-#16 STANDARD	5 63459-3
#14-#15	#15-#16 TIN	63459-2
OBsolete	#15-#16 VARNISH RESIST OVER TIN	63459-1
ALUMINUM	COPPER	
MAGNET WIRE RANGE		4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN JR RUTH 1/26/87	
	0 PLC ± -	CHK G YETTER 1/29/87	
	1 PLC ± -	APVD J SWARTZ 1/29/87	
	2 PLC ± -	PRODUCT SPEC	
MATERIAL BRASS	FINISH SEE TABLE	NAME	TAB, .250 FASTON, MAG-MATE™ SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-63459 SCALE 4:1 SHEET 1 of 1 REV H4

CUSTOMER DRAWING