

1) Emitter, 2) Receiver, 3) Optical axis



Basic features

Approval/Conformity	CE UKCA WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Optical sensor head
Reference base unit	BAE SA-OH-059-...
Series	G04
Style	Cylinder Straight optics

Electrical connection

Cable diameter D	1.80 mm
Cable length L	1 m
Connection	Cable with connector, M8x1- Female, 1 m, PUR

Environmental conditions

Ambient temperature	-10...55 °C
IP rating	IP65

Interface

Switching output	for switching amplifier
------------------	-------------------------

Remarks

For additional information, refer to user's guide.

Material

Housing material	Stainless steel
Material jacket	PUR
Material sensing surface	PMMA

Mechanical data

Dimension	Ø 4 x 11.7 mm
Mounting part	Diameter 4.0 mm


Optical features

Beam characteristic	divergent, max. 2.5°
LED group per IEC 62471	Exempt Group
Light spot size	Ø 10 mm at 100 mm
Light type	microSPOT-LED red light
Principle of optical operation	Through-beam sensor
Smallest part typ.	0.40 mm
Wave length	650 nm

Range/Distance

Range	0...2 m
Rated operating distance Sn	2000 mm

Connector Drawings



Opto Symbols

