


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		REVISED PER ECN-25-319843	05MAY2025	MS	JM










1. ALL DIMENSIONS ARE IN MILLIMETERS [IN].
2. DIMENSIONS APPLY AFTER FINISHING.
3. MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
4. USE MINIMUM BEND RADIUS FOR MATERIAL TYPE AND TEMPER. NO CRAZING ACCEPTABLE ON BENT PARTS.
5. LINX LOGO ENBOSSED AS SHOWN .05 [0.002"] DEPTH MINIMUM. ARTWORK PROVIDED VIA LINX-LOGO-BLACK-ABBREVIATED.PDF SIZED AND POSITIONED APPROX. AS SHOWN.
6. PACKAGE PER ORDER AND LABEL BAG, BOX, AND REEL IAW LABEL DRAWING PROVIDED.
7. THERE ARE TWO PACKAGING OPTIONS FOR THIS PRODUCT.
 1. PE BAG PACKAGING
 2. TAPE OR REEL
8. FINISH TO BE BRIGHT NICKEL, FREE OF CONTAMINATES AND UNDAMAGED BY REFLOW TEMPERATURES.
9. UNLISTED GEOMETRY CONTROLLED BY MODEL AT LATEST REVISION.

TAPE AND REEL	BAT-HLD-001-TR
PE BAGS	BAT-HLD-001
PACKAGE	PN NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	07JAN2025	TE Connectivity Ltd.
		CHK	07JAN2025	
		APVD	07JAN2025	
		PRODUCT SPEC	108-161665	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME
0 PLC ± - 1 PLC ± 0.30 2 PLC ± 0.25 3 PLC ± 0.20 4 PLC ± 0.10 ANGLES ± 1°		APPLICATION SPEC		BATTERY HOLDER CR2032 SURFACE MOUNT
MATERIAL PHOSPHOR BRONZE C5191 T=0.25mm		FINISH NICKEL		SIZE A2
		WEIGHT -		CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO BAT-HLD-001-XX
		SCALE 1:1		RESTRICTED TO -
		SHEET 1 of 3		REV F

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



Technical requirements:

- The cumulative allowable tolerance for the distance between ten circular holes is $\pm 0.2\text{mm}$
- With a length of 250mm, the allowable bending degree is 1mm
- The material thickness shall be measured at the edge of the carrier tape
- All dimensions are defined according to the EIA-481-C standard
- Material: Black PS T=0.35mm
- All rollers are gray blue hollow rotating plastic rollers
- Overall molding length: 13.5M,
- Non specified tolerance range: $\pm 0.1\text{mm}$; Exceeding 250mm does not calculate cumulative error
- The chamfer R of any unmarked part of the cavity shape is 0.2-0.3; The draft angle not marked is below 3°

Packaging information:





- Each roll contains 650 products, with relevant labels attached to the outside of the roll;
- Put every 8 rolls in a plastic bag;
- Each outer box contains 8 plates, with a total of 5200 products;
- Seal the top and bottom of the outer box with adhesive tape to form the character "工";
- Battery shrapnel packaging material TER161 SMT roll (MY-AA-03-R)

PACKAGING FOR PN BAT-HLD-001-TR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MADHAN_S 07JAN2025	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK MOHANTY, JAGRUTI 07JAN2025		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MOHANTY, JAGRUTI 07JAN2025	NAME	
0 PLC $\pm -$		PRODUCT SPEC		BATTERY HOLDER CR2032 SURFACE MOUNT
1 PLC ± 0.30		APPLICATION SPEC		
2 PLC ± 0.25		108-161665		SIZE A2
3 PLC ± 0.20		-		CAGE CODE 00779
4 PLC ± 0.10		-		DRAWING NO C-BAT-HLD-001-XX
ANGLES $\pm 1^\circ$		-		RESTRICTED TO -
MATERIAL PHOSPHOR BRONZE C5191 T=0.25mm		FINISH NICKEL		SCALE 1:1
		WEIGHT -		SHEET 2 of 3
		CUSTOMER DRAWING		REV F

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

Seal the top and bottom of the outer box with adhesive tape to form the character "I".



PACKAGING FOR PN BAT-HLD-001

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MADHAN_S 07JAN2025	TE Connectivity Ltd.																			
DIMENSIONS: mm		CHK MOHANTY, JAGRUTI 07JAN2025																				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MOHANTY, JAGRUTI 07JAN2025	NAME BATTERY HOLDER CR2032 SURFACE MOUNT																			
<table border="0"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>0.30</td></tr> <tr><td>2 PLC</td><td>±</td><td>0.25</td></tr> <tr><td>3 PLC</td><td>±</td><td>0.20</td></tr> <tr><td>4 PLC</td><td>±</td><td>0.10</td></tr> <tr><td>ANGLES</td><td>±</td><td>1°</td></tr> </table>		0 PLC	±	-	1 PLC	±	0.30	2 PLC	±	0.25	3 PLC	±	0.20	4 PLC	±	0.10	ANGLES	±	1°	PRODUCT SPEC 108-161665	RESTRICTED TO	
0 PLC	±	-																				
1 PLC	±	0.30																				
2 PLC	±	0.25																				
3 PLC	±	0.20																				
4 PLC	±	0.10																				
ANGLES	±	1°																				
MATERIAL PHOSPHOR BRONZE C5191 T=0.25mm		FINISH NICKEL	WEIGHT -	SIZE A2																		
		CUSTOMER DRAWING	CAGE CODE 00779	DRAWING NO C-BAT-HLD-001-XX																		
		SCALE 1:1	SHEET 3 of 3	REV F																		