

1) Emitter, 2) Receiver, 3) Optical axis



### Basic features

Approval/Conformity	CE UKCA WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Optical sensor head
Reference base unit	BAE SA-OH-059-...
Series	Q06
Style	Square Connection 90°

### Electrical connection

Cable diameter D	1.80 mm
Cable length L	1 m
Connection	Cable with connector, M8x1-Female, 1 m, PUR

### Environmental conditions

Ambient temperature	-10...55 °C
IP rating	IP65

### Interface

Switching output	for switching amplifier
------------------	-------------------------

### Material

Housing material	Brass, nickel-plated
Material jacket	PUR
Material sensing surface	PMMA
Surface protection	nickel-plated

### Mechanical data

Dimension	12 x 6 x 6 mm
Mounting part	Screw M2

## Optical features

Beam characteristic	divergent, max. 2.5°
LED group per IEC 62471	Exempt Group
Light spot size	Ø 10 mm at 100 mm
Light type	microSPOT-LED red light
Principle of optical operation	Through-beam sensor

Smallest part typ.	0.40 mm
Wave length	650 nm


## Range/Distance

Range	0...2 m
Rated operating distance Sn	2000 mm

## Remarks

For additional information, refer to user's guide.

## Connector Drawings



## Opto Symbols

