


DO NOT SCALE FROM THIS PRINT

MIT-XXX-01-X-D-EMX



No OF POSITIONS
-019, -038, -057, -076, -095 (PER ROW)

LEAD STYLE
-01: .1780 [4.521]

EDGE MOUNT THICKNESS
-EM2: .062[1.57]

ROW SPECIFICATION
-D: DOUBLE (USE MIT-19-01-D-XX-N)

No OF BANKS

PLATING SPECIFICATION
 -L: LIGHT SELECTIVE GOLD (USE T-1S42-01-L & T-1G24-01-L)
 -H: HEAVY GOLD (USE T-1S42-01-H & T-1G24-01-G)






TABLE 1

No OF POSITIONS	GND PLANE COPLANARITY
-019 THRU -057	.004 [.10]
-076, -095	.005[1.27]



- NOTES:
- ⊕ REPRESENTS A CRITICAL DIMENSION.
 - CONTACT RETENTION: 8 OZ MIN.
 - GROUND PLANE RETENTION: 12 OZ MIN.
 - PARTS ARE MOLD TO POSITION.
 - MAX VARIANCE OF .002[0.05].
 - SEE WWW.SAMTEC.COM/PROCESSING/EDGEMOUNT_TECTALK/INDEX.HTM FOR INFORMATION ON PROCESSING EDGEMOUNT PARTS TO BOARDS.
 - MAX ALLOWABLE BOW: .002[0.05] IN/IN AFTER ASSEMBLY.
 - PARTS TO BE PACKAGED IN TRAYS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE: DECIMALS ANGLES .XX: ±.01[.3] 2° .XXX: ±.005[.13] .XXXX: ±.0020[.051]	PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.	520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322