


REVISIONS

REV	DESCRIPTION	DATE	DWN	APVD
AA	(ECN-IAS-04857) INITIAL RELEASE	20NOV15	S.S.	R.H.
AA1	CHANGE TO TE DRAWING FORMAT	21MAR25	KS	C.HANG

PARAMETER	PERFORMANCE
MODEL NUMBER	NMDHPCNSMAM518
FREQUENCY	0 - 6 GHz
WEIGHT	217g
IP RATING	OUT DOOR RATED
OPERATING TEMP	-30 C TO +85 C
CABLE TYPE	DUAL - SHIELDED LOW LOSS COAXIAL CABLE
CABLE LENGTH	5180
CONNECTOR	SMA - MALE INSTALLED
MOUNT TYPE	NMD
INSTALLATION HOLE SIZE	19.05[.750]
HARDWARE	□-RING AND NMD RING ADAPTER INCLUDED



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. SAFVI 20NOV2015

CHK YJ TEQH 20NOV2015

APVD C.HANG 20NOV2015

PRODUCT SPEC REFER TABLE

APPLICATION SPEC N/A

WEIGHT REFER TABLE

CUSTOMER DRAWING




MOUNT, BMM, 3/4, A195, SMAM

DIMENSIONS: mm[INCH]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ± 0.5
- 1 PLC ± 0.25
- 2 PLC ± 0.130
- 3 PLC ±
- 4 PLC ±
- ANGLES ± 30'



MATERIAL N/A

FINISH N/A

NAME

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 © NMDHPCNSMAM518M0

SCALE 1:2 SHEET 1 OF 1 REV AA1