


TAT-125 ADHESIVE LINED TUBING  
 POLYOLEFIN, FLEXIBLE, HEAT-SHRINKABLE, DUAL WALL TUBING

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
4		REVISED PER ECO-18-008718	16MAY2018	J.B
A		REDRAWN IN CREO	18NOV2025	RT

PART AS SUPPLIED AND FULLY RECOVERED



EXPANDED AS SUPPLIED

FULLY RECOVERED AFTER HEATING




TABLE 1: DIMENSIONS mm(inches)

SIZE	AS SUPPLIED		AS RECOVERED					
	EXPANDED I.D (D)		MAXIMUM(d)		NOMINAL TOTAL WALL (W)		NOMINAL ADHESIVE WALL (W1)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.
1/8	3.18	0.125	1.57	0.062	0.69	0.027	0.23	0.009
3/16	4.75	0.187	2.36	0.093	0.71	0.028	0.25	0.010
1/4	6.35	0.250	3.18	0.125	0.74	0.029	0.13	0.005
3/8	9.53	0.375	4.75	0.187	0.74	0.029	0.13	0.005
1/2	12.7	0.500	6.35	0.250	0.76	0.030	0.15	0.006
3/4	19.05	0.750	9.53	0.375	0.89	0.035	0.15	0.006
1	25.40	1.000	12.7	0.500	1.07	0.042	0.20	0.008
1-1/2	38.10	1.500	19.05	0.750	1.19	0.047	0.28	0.011
2	50.80	2.000	25.40	1.000	1.65	0.065	0.56	0.022
3	76.20	3.000	38.10	1.500	1.65	0.065	0.56	0.022
4	101.60	4.000	50.80	2.000	1.78	0.070	0.51	0.020

PRODUCT INFORMATION

- SHRINK RATIO 2:1
- STANDARD COLOR: BLACK  
NON-STANDARD : WHITE, RED, BLUE, YELLOW, GREEN, ORANGE, BROWN, VIOLET & CLEAR
- FLAME RETARDANT (EXCEPT CLEAR)
- REFERENCED SPECIFICATION : TEC-108-120011
- TUBING OF SPECIAL EXPANDED OR RECOVERED DIMENSIONS MAY BE SUPPLIED AS SPECIFIED IN THE CONTRACT OR ORDER
- PRODUCT AVAILABLE IN DIFFERENT CUT LENGTHS
- STANDARD STICK LENGTH - 1220mm

CUT LENGTH	UP TO 9.9mm	±1.5mm	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN	18NOV2025	TE Connectivity
	10 TO 24.9mm	±1.5mm		CHK	18NOV2025	
25 TO 54.9mm	±1.5mm		DIMENSIONS:	mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME TAT-125 POLYOLEFIN TUBING
55 TO 99.9mm	±3.0mm			0 PLC	±	PRODUCT SPEC TEC-108-120011
100 TO 149.9mm	±4.0mm			1 PLC	±0.1	APPLICATION SPEC 114-120023
150 TO 499.9mm	±5.0mm		2 PLC	±0.01	WEIGHT CUSTOMER DRAWING	SIZE A2 CAGE CODE - DRAWING NO. G-TAT-125 RESTRICTED TO -
500mm AND GREATER	±25.4mm		3 PLC	±0.001	SCALE NTS	SHEET 1 OF 1
			4 PLC	±0.0001		REV A
			ANGLES	±		
			FINISH			