



1) Sensing surface



Basic features

Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Inductive sensor

Display/Operation

Power indicator	no
-----------------	----

Electrical connection

Cable diameter D	4.65 mm
Cable length L	5 m
Conductor cross-section	0.34 mm ²
Connection type	Cable, 5.00 m, PVC
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	1 µF
Min. operating current I _m	0 mA
No-load current I _o max., damped	5 mA
No-load current I _o max., undamped	2 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	Open collector
Protection class	II
Rated insulation voltage U _i	250 V AC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	21 ms
Residual current I _r max.	30 µA
Ripple max. (% of U _e)	15 %
Switching frequency	3500 Hz
Utilization category	DC -13
Voltage drop static max.	1.5 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP68, according to BWN Pr 20

Functional safety

MTTF (40 °C)	850 a
--------------	-------

Interface

Switching output PNP normally open (NO)

Material

Housing material Brass, Nickel-free coated
Material jacket PVC
Material sensing surface PBT

Mechanical data

Dimension $\varnothing 12 \times 33$ mm
Installation for flush mounting
Mounting length 27 mm
Size M12x1
Tightening torque 10 Nm

Range/Distance

Assured operating distance S_a 1.6 mm
Hysteresis H max. (% of S_r) 15.0 %
Rated operating distance S_n 2 mm
Real switching distance s_r 2 mm
Repeat accuracy max. (% of S_r) 5.0 %
Temperature drift max. (% of S_r) 10 %
Tolerance S_r ± 10 %

Remarks

The sensor is functional again after the overload has been eliminated.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams (Schematic)

