



1) Sensing surface



Basic features

Approval/Conformity	CE UKCA cULus WEEE
Base type deviation	Pot core and housing coated
Basic standard	IEC 60947-5-2
Principle of operation	Inductive sensor

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Cable diameter D	2.50 mm
Cable length L	2 m
Conductor cross-section	0.10 mm ²
Connection type	Cable, 2.00 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U _e	0.2 µF
No-load current I _o max., damped	10 mA
No-load current I _o max., undamped	3 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	Open collector
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	100 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	20 ms
Residual current I _r max.	50 µA
Ripple max. (% of U _e)	15 %
Switching frequency	5000 Hz
Utilization category	DC -12
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Functional safety

MTTF (40 °C)	305 a
--------------	-------

Interface

Switching output PNP normally open (NO)

Material

Housing material Brass, coated
 Material jacket PUR
 Material sensing surface Ceramic

Mechanical data

Dimension 16 x 8 x 4.7 mm
 Installation for flush mounting
 Size 16x8x4.7

Range/Distance

Assured operating distance Sa 1.6 mm
 Hysteresis H max. (% of Sr) 15.0 %
 Rated operating distance Sn 2 mm
 Real switching distance sr 2 mm
 Repeat accuracy max. (% of Sr) 1.0 %
 Switching distance marking ■■
 Temperature drift max. (% of Sr) 10 %
 Tolerance Sr ±10 %

Remarks

The sensor is functional again after the overload has been eliminated.
 Cable weld bead resistant
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams (Schematic)

