



MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
1211930007	T05007B30M003	0.3 M +1.9 CM/-0 [1.0' +0.75"/-0]
1211930008	T05007B30M010	1.0 M +5.6 CM/-0 [3.3' +2.19"/-0]



T05007B30M020

WIRE TYPE
0.34mm² [22 AWG] BLACK

CABLE LENGTH
M003----0.3 METER
M020----2 METER
M100----10 METER

MECHANICAL
CONTACT : GOLD/NICKEL OVER COPPER ALLOY
INSERT : BLACK NYLON
COUPLING NUT: NICKEL PLATED COPPER ALLOY
MOLDED BODY: BLACK TPE
CABLE: 0.34mm² [22 AWG] 5 CONDUCTORS BLACK JACKET
WRAP LABEL: MYLAR YELLOW WITH BLACK LETTERS

ELECTRICAL
VOLTAGE RATING: 250V AC/DC
AMPERAGE: 4A

ENVIRONMENTAL
PROTECTION: IP67

OPERATION TEMP: -20°C~80°C

THE RECOMMENDED FEMALE CONNECTOR SHOULD HAVE
NICKEL PLATING ON THE FEMALE THREADS

INITIAL RELEASE EC NO: IPG2014-1611 DRWN: KJOZWIK 2014/04/25 CHKD: VOU APPR: BWOODMAN2014/05/09		DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH [MM]		SCALE 1:1	DESIGN UNITS INCH	◎ □ THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY DATE KJOZWIK 2014/02/13		TITLE MIC 5P PUSHLOCK 90 DEGREE BLACK TPU			
				4 PLACES	±---	±---	CHECKED BY DATE VOU 2014/04/25					
				3 PLACES	±---	±---	APPROVED BY DATE BWOODMAN 2014/05/09		molex MOLEX INCORPORATED			
				2 PLACES	±---	±---						
				1 PLACE	±---	±---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-121193-002			SHEET NO. 1 OF 1
				ANGULAR ±.5°			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
A	REV											