

20

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.



THIS DRAWING IS UNPUBLISHED.

BY -



© COPYRIGHT 20

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	K	REVISED PER ECR-14-011136	04AUG2014	NK	DC



Para lengüeta de 0.8 mm  
For 0.8mm tab thickness




SECTION D-D  
SCALE 4:1




SECTION C-C  
SCALE 4:1

336075-7 (REELED WITH PAPER INTERLEAVE)	Latón Brass	Preestañado Pre-Tin
336075-6	CuNiSi	Preestañado Pre-Tin
336075-5	Acero Steel	Pre-niquelado Pre-Ni
336075-3	Latón Brass	Preestañado Pre-Tin
336075-1	Latón Brass	-
Guion Dash	Material	Acabado Finish



Left-sided product



Right-sided product

Rango de hilo de 0,5 a 1,5 mm<sup>2</sup>  
Wire range from 0.5 to 1.5 mm<sup>2</sup>  
Diámetro de aislante max 3,0 mm  
Max. Insulation Diameter 3.0 mm

DIMENSIONS:

mm

DWN  
J. Saló 22 Dec 04

CHK  
L. Lázaro 22 Dec 04

APVD  
-

PRODUCT SPEC  
108-22128 Brass  
108-22150 Pre-Ni Steel

APPLICATION SPEC  
114-22017

WEIGHT  
-

MATERIAL

Table

FINISH

Table

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.5
1 PLC	±0.5
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±



TE Connectivity

NAME  
E-SPRING CONTACT 6,35 Receptaculo  
6.35 Receptacle E-SPRING CONTACT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C=336075	-

Customer Drawing

SCALE 4:1

SHEET 1 OF 1

REV K