



LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E5	REVISED PER ECR-13-011067	16JUL13	KH	PD



SUGGESTED MATING TAB



- 1 - MATL: ½H BRASS OR NICKEL PL STEEL.
- 2 - NO BURRS PERMISSIBLE AT HOLE.
- 3 - MUST BE FLAT WITHIN 0.076[.003] OVER THIS LENGTH.
- 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
- 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076[.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 DFE SYMBOL PER TABLE
- 2 PREPRODUCTION - FASR REQUIRED
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	7/3/96	 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK	M FEHER	7/3/96						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J GILLESPIE	7/3/96	NAME HOUSING, RECTPT, POSITIVE-LOCK, MKIII, 2 CIRCUIT, 6.35 [.250] SERIES —				
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.25 [.010] 4 PLC ± —		PRODUCT SPEC —							
	ANGLES ± ±		APPLICATION SPEC —							
MATERIAL	FINISH	WEIGHT	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
SEE TABLE	SEE TABLE			A2	00779	C=521119		—		
CUSTOMER DRAWING					SCALE	4:1	SHEET	1 of 2	REV	E5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC

DIST

AF50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

>PA<	BROWN	66/6 NYLON,V0	2	1-521119-7
>PA<	YELLOW	66/6 NYLON,V0	2	1-521119-6
>PA<	GREEN	66/6 NYLON,V0	2	1-521119-5
>PA<	BLACK	66/6 NYLON,V0	2	1-521119-4
>PA<	RED	66/6 NYLON,V0	2	1-521119-3
>PA<	BLUE	66/6 NYLON,V0	2	1-521119-2
>PA<	NATURAL	66/6 NYLON,V0	2	1-521119-1
>PA<	BROWN	6/6 NYLON,V2	2	1-521119-0
>PA<	YELLOW	6/6 NYLON,V2	2	521119-9
>PA<	GREEN	6/6 NYLON,V2	2	521119-8
>PA<	BLACK	6/6 NYLON,V2	2	521119-7
>PA<	RED	6/6 NYLON,V2	2	521119-6
>PA<	NATURAL	6/6 NYLON,V2	2	521119-5
>PA<	BLUE	6/6 NYLON		521119-4
>PA<	PUTTY		6	521119-2
>PA<	NATURAL			521119-1
DFE SYMBOL	COLOR	MATERIAL	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.25 [.010]

4 PLC ± -

ANGLES ± -

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

FINISH

SEE TABLE

DWN
JR RUTH
7/3/96

CHK
M FEHER
7/3/96

APVD
J GILLESPIE
7/3/96

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

HOUSING, RECTPT, POSITIVE-LOCK,
MKIII, 2 CIRCUIT, 6.35 [.250] SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C=521119

SCALE

SHEET

REV

1471-9 (3/11)

52119

5